



C/232 Venus Set

200 ml / h: 64 mm / Ø 92 mm



- Imprint on the handle
- Imprint on the inside
- Imprint on the bottom inside
- Imprint on the bottom outside

- 50 x 6 mm
- 40 x 20 mm
- Ø 30 mm
- Ø 20 mm

*In the case of projects for transfer print running outside of the standard print area, please contact our sales department.



[How to prepare print material](#)

meaning

- Transfer Print
- Sensitive Touch
- Direct Print

C/232 Venus Set

130 ml / h: 59 mm / Ø 78 mm



- Imprint on the handle
- Imprint on the inside
- Imprint on the bottom inside
- Imprint on the bottom outside

- 50 x 6 mm
- 40 x 20 mm
- Ø 30 mm
- Ø 20 mm

*In the case of projects for transfer print running outside of the standard print area, please contact our sales department.




[How to prepare print material](#)

meaning

- Transfer Print
- Sensitive Touch
- Direct Print

C/232 Venus Set

80 ml / h: 55 mm / Ø 63 mm



Imprint on the handle

Imprint on the inside

Imprint on the bottom inside

Imprint on the bottom outside

- 50 x 6 mm

- 30 x 15 mm

- Ø 10 mm

- Ø 15 mm

*In the case of projects for transfer print running outside of the standard print area, please contact our sales department.

[How to prepare print material](#)

meaning

- Transfer Print
- Sensitive Touch
- Direct Print